




Plastic Fiber Optic Holder
LPFHOLD

MODELO: LPFHOLD

Plastic Fiber Optic Holder

Material: Plastic
Length: 6.8cm





Plastic Fiber Optic Holder
LPFHOLD


MODELO: LPFHOLD

Operating steps

1. Put the coated optical fiber into the stripping surface.



2. Hold your left hand gently and pull your right hand down.



3. Pull the cable out and strip the coating.



4. Peeled optical fibers, wiped with dust-free paper and alcohol.



5. Optical fibers are placed on the fixed length surface and into the cutting tool chuck.



6. Use the cutting knife to complete the cutting.

